

PRODUCT REQUIREMENT SHEET	
See LV 75-32	
MEASURING VOLTAGE	240V (stabilisation 3 min.)
MEASURING POSITION	Horizontal
LIFE TEST POSITION	One lamp in free air and one lamp in luminair
BURNING POSITION	P15
SWITCHING CYCLE	Continuous
AGEING	1h at rated voltage

PRODUCT REQUIREMENT SHEET	
See LV 75-32	
MEASURING VOLTAGE	240V (stabilisation 3 min.)
MEASURING POSITION	Horizontal
LIFE TEST POSITION	One lamp in free air and one lamp in luminair
BURNING POSITION	P15
SWITCHING CYCLE	Continuous
AGEING	1h at rated voltage

PRODUCT REQUIREMENT SHEET	
See LV 75-32	
MEASURING VOLTAGE	240V (stabilisation 3 min.)
MEASURING POSITION	Horizontal
LIFE TEST POSITION	One lamp in free air and one lamp in luminair
BURNING POSITION	P15
SWITCHING CYCLE	Continuous
AGEING	1h at rated voltage